



### Main

Range name	Sedna
Range	Sedna
Device application	Mounting
Function	Cover frame
Number of gangs	3 gangs
Installation direction	Horizontal
Range compatibility	Sedna socket-outlet
Cover frame color	Graphite

### Complementary

Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Height	85 mm
Width	227 mm
Depth	9.7 mm
Depth of visual part	9.7 mm
Net weight	0.036 kg






### Environment

IP degree of protection	IP44
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	8.500 cm
Package 1 Length	23.000 cm
Package 1 Weight	41.400 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	10.000 cm
Package 2 Width	20.500 cm
Package 2 Length	31.500 cm
Package 2 Weight	929.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	100
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	5.299 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations