



## Main

Range of product	Altivar
Product or component type	Encoder interface card
Range compatibility	Altivar 61 Altivar Process Modular Altivar 71Q Altivar 61Q Altivar 71 Altivar Lift
Discrete output type	Open collector
[Us] rated supply voltage	15 V DC (voltage limits: 15...16 V)
Number of pulses per revolution	10000 for ATV71H.....383 5000 for all ATV61 drives 5000 for ATV71H...M3 5000 for ATV71H...M3X 5000 for ATV71H...N4

## Complementary

Maximum supply current	0.175 A
Protection type	Overload protection Short-circuit protection
Maximum cable distance between devices	500 m
Maximum operating frequency	300 kHz
Input signal	A B Compliment of A Compliment of B/AB/A
Input impedance	1 kOhm
Electrical connection	Terminal, connection capacity: 0.2 mm <sup>2</sup> (AWG 24) <100 m cable length, encoder, 100 mA at 10 V Terminal, connection capacity: 0.2 mm <sup>2</sup> (AWG 24) <100 m cable length, encoder, 175 mA at 10 V Terminal, connection capacity: 0.2 mm <sup>2</sup> (AWG 24) <200 m cable length, encoder, 100 mA at 10 V Terminal, connection capacity: 0.2 mm <sup>2</sup> (AWG 24) <200 m cable length, encoder, 175 mA at 10 V Terminal, connection capacity: 0.5 mm <sup>2</sup> (AWG 20) <500 m cable length, encoder, 100 mA at 10 V Terminal, connection capacity: 0.5 mm <sup>2</sup> (AWG 20) <500 m cable length, encoder, 175 mA at 10 V
Net weight	0.2 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.500 cm
Package 1 Width	17.000 cm
Package 1 Length	23.000 cm
Package 1 Weight	150.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Height	30.000 cm

Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.470 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

### Contractual warranty

Warranty	18 months
----------	-----------