



Main

Range name	Cedar Plus
Product or component type	Switch
Function	1-pole
Delivery form	Complete product
Pilot light	Without pilot lamp
Cover plate color	Grey

Complementary

Installation	Surface
Power range	3680 W
Rated current	16 AX at 250 V AC
Kind of terminals	Lift terminals
Terminal capacity	2 cable(s) 2.5 mm ²
Wire structure	Flexible Rigid
Wire stripping length	11 mm
Material of visible parts	PA6 FR850
Surface finish	Glossy
Height	79 mm
Width	66 mm
Depth	48 mm
Net weight	0.095 kg

Environment

Product certifications	KEMA
IP degree of protection	IP44

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	7.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	97.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.000 cm
Package 2 Weight	1.071 kg
Unit Type of Package 3	S03
Number of Units in Package 3	60

Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.828 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------