

Product data sheet

Characteristics

GCKRN50A2G

Exclusive - 2-pole switch with indicator lamp - 2 gangs - 50 A - white



Main

Product or component type	Switch with indicator lamp
Device presentation	Complete product
Colour tint	White
Quantity per set	Set of 5

Complementary

Switch function	2-pole
Control type	Dolly switch
Number of gangs	2 gangs
Pilot light	Red neon indicator
Device mounting	Wall mounted
Rated current	50 A at 230 V AC
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Surface finish	Matt
Height	86 mm
Width	146 mm
Depth	36 mm
Net weight	0.208 kg

Environment


Standards	BS EN 60669-1
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.5 cm
Package 1 Length	14.6 cm
Package 1 Weight	211.1 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	9.5 cm
Package 2 Width	15.5 cm
Package 2 Length	18.5 cm
Package 2 Weight	1.141 kg

Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	34 cm
Package 3 Width	39 cm
Package 3 Length	50 cm
Package 3 Weight	23.52 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------