

Product data sheet

Characteristics

GRO

Exclusive - ceiling rose - 150 W - white



Main

Range of product	Exclusive
Product or component type	Ceiling rose
Device presentation	Complete product
Colour tint	White
Quantity per set	Set of 10

Complementary

Device mounting	Ceiling
Fixing mode	By screws
Current consumption	6 A
Rated lamp wattage	150 W
Material	Urea (carbamide)
Type of installation	Indoor
Height	88 mm
Length	88 mm
Width	32 mm
Net weight	0.082 kg

Environment

Standards	BS 67 BS EN 61184
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	9 cm
Package 1 Length	9 cm
Package 1 Weight	81.8 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	14 cm
Package 2 Length	18.6 cm
Package 2 Weight	904.7 g
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	30 cm

Package 3 Width	39.2 cm
Package 3 Length	50 cm
Package 3 Weight	18.693 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------