



Fő jellemzők

Termék vagy alkatrész típusa	Valve
Valve type	Globe
Valve product series	V222
Valve model	V222/125/250
Medium compatibility	Glycol 25 % Glycol 30 % Glycol 50 % Water
Valve configuration	2-Way
Valve connection type	Flanged
Valve connection size	DN125 (ISO 7005-2)
Body size	125 mm (5 in)
Pipe size	125 mm
Flow characteristic	Equal percentage
Flow coefficient	289.06 cv 250 kvs
Pressure class	PN16
Operating fluid temperature	-10...150 °C
Pressure fluid max delta P normal life	103,42 kPa
Control valve rangeability	Greater than 50:1
Stroke length	50 mm
Seat leakage	Port A: Less than 0.05 % of kvs
Stem flow action	Stem down closed
Stem movement	Linear
Trim material	Stainless steel
Test anyaga	Grey cast iron GG-25
Seat material	Port A: stainless steel AISI 420
Stem material	Stainless steel AISI 420
Plug material	Stainless steel AISI 420
Stem seal material	EPDM (ethylene propylene diene monomer)
Seating seal material	Port A: metal to metal
Packing material	Spring-loaded PTFE v-ring
Targeted region	Europe Asia Pacific. Australia.

Csomagolási egység

1. csomag-csomagolási egység típusa	PCE
Egységek száma 1. csomagban	1
1. csomag magassága	25,0 cm
1. csomag szélessége	39,0 cm
1. csomag hossza	48,0 cm
1. csomag súlya	57,0 kg

Kínálat fenntarthatósága

EU RoHS irányelv	Proaktív megfelelés (A termék nem tartozik az EU RoHS jogi hatálya alá)  EU RoHS nyilatkozat
Környezetvédelmi közzététel	 A Termék Környezeti Profilja
Körkörösségi profil	Nincs szükség specifikus újrahasznosítási műveletekre