

# 7214106000

## Kétjáratú menetes szabályzó szelep

### V241/15/0.25



#### Fő jellemzők

|                                        |                                                    |
|----------------------------------------|----------------------------------------------------|
| Valve product range                    | Venta                                              |
| Termék vagy alkatrész típusa           | Valve                                              |
| Valve type                             | Globe                                              |
| Valve product series                   | V241                                               |
| Valve model                            | V241/15/0.25                                       |
| Medium compatibility                   | Glycol 25 %<br>Glycol 30 %<br>Glycol 50 %<br>Water |
| Valve configuration                    | 2-Way                                              |
| Valve connection type                  | G External                                         |
| Valve connection size                  | G 1B                                               |
| Pipe size                              | 15 mm                                              |
| Body size                              | 15 mm (1/2 in)                                     |
| Flow characteristic                    | Equal percentage                                   |
| Flow coefficient                       | 0.29 cv<br>0.25 kvs                                |
| Pressure class                         | PN16                                               |
| Operating fluid temperature            | -20...150 °C                                       |
| Pressure fluid max delta P normal life | 599,84 kPa                                         |
| Control valve rangeability             | Greater than 50:1                                  |
| Stroke length                          | 20 mm                                              |
| Seat leakage                           | Port A: Less than 0.02 % of kvs                    |
| Stem flow action                       | Stem up closed                                     |
| Stem movement                          | Linear                                             |
| Trim material                          | Stainless steel                                    |
| Test anyaga                            | Bronze Rg5                                         |
| Seat material                          | Port A: stainless steel AISI 303                   |
| Stem material                          | Stainless steel AISI 303                           |
| Plug material                          | Stainless steel AISI 303                           |
| Stem seal material                     | EPDM (ethylene propylene diene monomer)            |
| Seating seal material                  | Port A: metal to metal                             |
| Packing material                       | EPDM (ethylene propylene diene monomer)            |
| Targeted region                        | Europe<br>Asia Pacific.<br>Australia.              |

#### Csomagolási egység

|                                     |         |
|-------------------------------------|---------|
| 1. csomag-csomagolási egység típusa | PCE     |
| Egységek száma 1. csomagban         | 1       |
| 1. csomag magassága                 | 5,0 cm  |
| 1. csomag szélessége                | 10,0 cm |
| 1. csomag hossza                    | 16,5 cm |
| 1. csomag súlya                     | 975,0 g |

## Kínai fenntarthatósága

|                             |                                                                                                                                |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS irányelv            | Nem alkalmazható, nem tartozik az EU RoHS jogi hatálya alá                                                                     |
| Kínai RoHS rendelet         | <a href="#"> Kínai RoHS Nyilatkozat</a>       |
| Környezetvédelmi közzététel | <a href="#"> A Termék Környezeti Profilja</a> |
| Körköröségi profil          | Nincs szükség specifikus újrahasznosítási műveletekre                                                                          |