



### Fő jellemzők

|                                        |                                                                                              |
|----------------------------------------|----------------------------------------------------------------------------------------------|
| Valve product range                    | Venta                                                                                        |
| Termék vagy alkatrész típusa           | Valve                                                                                        |
| Valve type                             | Globe                                                                                        |
| Valve product series                   | V341                                                                                         |
| Valve model                            | V341/15/4.0                                                                                  |
| Medium compatibility                   | Glycol 25 %<br>Glycol 30 %<br>Glycol 50 %<br>Water                                           |
| Valve configuration                    | 3-Way                                                                                        |
| Valve connection type                  | G External                                                                                   |
| Valve connection size                  | G 1B                                                                                         |
| Body size                              | 15 mm (1/2 in)                                                                               |
| Pipe size                              | 15 mm                                                                                        |
| Flow characteristic                    | Equal percentage                                                                             |
| Flow coefficient                       | 4.62 cv<br>4 kvs                                                                             |
| Pressure class                         | PN16                                                                                         |
| Operating fluid temperature            | -20...150 °C                                                                                 |
| Pressure fluid max delta P normal life | 599,84 kPa                                                                                   |
| Control valve rangeability             | Greater than 50:1                                                                            |
| Stroke length                          | 20 mm                                                                                        |
| Seat leakage                           | Port A: Less than 0.02 % of kvs (Ports A-AB)<br>Port A: Less than 0.05 % of kvs (Ports B-AB) |
| Stem flow action                       | Stem up closes A and opens B to AB                                                           |
| Stem movement                          | Linear                                                                                       |
| Trim material                          | Stainless steel                                                                              |
| Test anyaga                            | Bronze Rg5                                                                                   |
| Seat material                          | Port A: stainless steel AISI 303<br>Port B: stainless steel AISI 303                         |
| Stem material                          | Stainless steel AISI 303                                                                     |
| Plug material                          | Stainless steel AISI 303                                                                     |
| Stem seal material                     | EPDM (ethylene propylene diene monomer)                                                      |
| Seating seal material                  | Port A: metal to metal                                                                       |
| Packing material                       | EPDM (ethylene propylene diene monomer)                                                      |
| Targeted region                        | Europe<br>Asia Pacific.<br>Australia.                                                        |

### Csomagolási egység

|                                     |          |
|-------------------------------------|----------|
| 1. csomag-csomagolási egység típusa | PCE      |
| Egységek száma 1. csomagban         | 1        |
| 1. csomag magassága                 | 5,0 cm   |
| 1. csomag szélessége                | 10,5 cm  |
| 1. csomag hossza                    | 18,0 cm  |
| 1. csomag súlya                     | 1,055 kg |

## Kínai fenntarthatósága

|                             |                                                                                                                                |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS irányelv            | Nem alkalmazható, nem tartozik az EU RoHS jogi hatálya alá                                                                     |
| Kínai RoHS rendelet         | <a href="#"> Kínai RoHS Nyilatkozat</a>       |
| Környezetvédelmi közzététel | <a href="#"> A Termék Környezeti Profilja</a> |
| Körköröségi profil          | Nincs szükség specifikus újrahasznosítási műveletekre                                                                          |