



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch
Product specific application	Hazardous location box
Device short name	9007CR
Body type	Fixed
Head type	Plunger head
Material	Metal
Fixing mode	By the body
Movement of operating head	Linear
Type of operator	Stainless steel spring return plunger (adjustable)
Switch actuation	On end
Type of approach	Vertical approach, 1 direction
Electrical connection	Screw-clamp terminals (AWG 22...AWG 12), 1...2
Cable entry	1 entry for 1/2" - 14 NPT conforming to ANSI B1.20.1
Number of poles	1
Contacts type and composition	NC-NO
Contact operation	Snap action
Positive opening	Without
Level or class	Class II Division 1 Groups E/F/G Class I Division 1 Groups B/C/D
Sale per indivisible quantity	1

Complementary

Body material	Aluminium
Head material	Zinc
Function available	-
Switch function	SPDT-DB
Contact form	Form Z
Contacts material	Silver contacts
Terminals description ISO n°1	(1-2)NC (3-4)NO
Minimum force for tripping	3 lbf
Repeat accuracy	+/- 0.001 in linear travel of cam
[Ie] rated operational current	1.2 A at 600 V AC, A600 conforming to NEMA 1.5 A at 480 V AC, A600 conforming to NEMA 3 A at 240 V AC, A600 conforming to NEMA 6 A at 120 V AC, A600 conforming to NEMA 0.1 A at 600 V DC, Q600 conforming to NEMA 0.27 A at 250 V AC, Q600 conforming to NEMA 0.55 A at 125 V DC, Q600 conforming to NEMA
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	600 V (pollution degree 3) conforming to UL 508 for contact block 600 V (pollution degree 3) conforming to CSA C22.2 No 14 for contact block

[Uimp] rated impulse withstand voltage	2.5 KV AC 1 min conforming to CE 2.2 KV AC 1 min conforming to UL 2.64 kV AC 1 s conforming to CSA
Short-circuit protection	10 A by CC fuse, protection type: non-time delay
Electrical durability	1000000 cycles
Local signalling	without
Mechanical durability	10000000 cycles
Width	69.09 mm
Height	180.59 mm
Depth	52.83 mm
Net weight	1.13 kg

Environment

Shock resistance	60 gn for 9 ms conforming to IEC 60068-2-27
Vibration resistance	25 gn (f= 10...150 Hz) conforming to IEC 60068-2-6
NEMA degree of protection	NEMA 1 conforming to Nema type 250 NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 6P conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 13 conforming to Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Electrical shock protection class	Class 0 conforming to IEC 61140
Ambient air temperature for operation	-29...85 °C for hazardous location
Ambient air temperature for storage	-29...85 °C
Environmental characteristic	Hazardous location
Protective treatment	Epoxy powder coat

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.452 cm
Package 1 Width	2.54 cm
Package 1 Length	16.387 cm
Package 1 Weight	1.134 kg

Offer Sustainability

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------