



Fő jellemzők

Valve product range	Venta
Termék vagy alkatrész típusa	Valve
Valve type	Globe
Valve product series	V232
Valve model	V232/50/38
Medium compatibility	Water Glycol 25 % Glycol 30 % Glycol 50 % Steam
Valve configuration	2-Way
Valve connection type	Flanged
Valve connection size	DN50 (ISO 7005-2)
Body size	50 mm (2 in)
Pipe size	50 mm
Flow characteristic	Equal percentage
Flow coefficient	43.94 cv 38 kvs
Pressure class	PN25
Operating fluid temperature	-20...150 °C
Pressure fluid max delta P normal life	799,79 kPa
Saturated steam temperature	-20...150 °C
Control valve rangeability	Greater than 200:1
Stroke length	20 mm
Seat leakage	Port A: Less than 0.02 % of kvs
Stem flow action	Stem up closed
Trim material	Stainless steel
Test anyaga	Nodular cast iron EN-JS 1025
Seat material	Port A: stainless steel AISI 303
Stem material	Stainless steel AISI 303
Plug material	Stainless steel AISI 303
Stem seal material	EPDM (ethylene propylene diene monomer)
Seating seal material	Port A: metal to metal
Packing material	EPDM (ethylene propylene diene monomer)
Targeted region	Europe Asia Pacific. Australia.

Csomagolási egység

1. csomag-csomagolási egység típusa	PCE
Egységek száma 1. csomagban	1
1. csomag magassága	16,5 cm
1. csomag szélessége	23,5 cm
1. csomag hossza	29,0 cm
1. csomag súlya	13,25 kg

Kínai fenntarthatósága

EU RoHS irányelv	Nem alkalmazható, nem tartozik az EU RoHS jogi hatálya alá
Kínai RoHS rendelet	 Kínai RoHS Nyilatkozat
Környezetvédelmi közzététel	 A Termék Környezeti Profilja
Körköröségi profil	Nincs szükség specifikus újrahasznosítási műveletekre