

Fő jellemzők

Termék vagy alkatrész típusa	Valve
Valve type	Globe
Valve product series	V321
Valve model	V321/80/100
Medium compatibility	Glycol 25 % Glycol 30 % Glycol 50 % Water
Valve configuration	3-Way
Valve connection type	Flanged
Valve connection size	DN80 (ISO 7005-2)
Body size	80 mm (3 in)
Pipe size	80 mm
Flow characteristic	Equal percentage
Flow coefficient	92.5 cv 80 kvs
Pressure class	PN16
Operating fluid temperature	-10...130 °C
Pressure fluid max delta P normal life	82,74 kPa
Control valve rangeability	Greater than 30:1
Stroke length	30 mm
Seat leakage	Port A: Less than 0.05 % of kvs
Stem flow action	Stem up closes A and opens B to AB
Stem movement	Linear
Trim material	Stainless steel
Test anyaga	Grey cast iron GG-25
Seat material	Port A: stainless steel AISI 420 Port B: stainless steel AISI 420
Stem material	Stainless steel 316Ti
Plug material	Stainless steel AISI 420
Stem seal material	EPDM (ethylene propylene diene monomer)
Seating seal material	Port A: metal to metal
Packing material	EPDM (ethylene propylene diene monomer)
Targeted region	Europe Asia Pacific. Australia.

Csomagolási egység

1. csomag-csomagolási egység típusa	PCE
Egységek száma 1. csomagban	1
1. csomag magassága	20,0 cm
1. csomag szélessége	32,0 cm
1. csomag hossza	34,5 cm
1. csomag súlya	22,35 kg

Kínálat fenntarthatósága

EU RoHS irányelv	Proaktív megfelelés (A termék nem tartozik az EU RoHS jogi hatálya alá)  EU RoHS nyilatkozat
Környezetvédelmi közzététel	 A Termék Környezeti Profilja
Körkörösségi profil	Nincs szükség specifikus újrahasznosítási műveletekre