

9007FTSB3M12

Limit switch, 9007, 9007FT foundry standard, spring return, CW+CCW, PG 13.5



Main

| | |
|-------------------------------|-------------------------|
| Range of Product | 9007 |
| Series name | Severe duty foundry |
| Product or Component Type | Limit switch |
| Device Application | Standard foundry switch |
| Device short name | 9007T/FT |
| Body type | Fixed |
| Head type | Rotary head |
| Sale per indivisible quantity | 1 |

Complementary

| | |
|--|--|
| Base plate style | Style B |
| Body material | Cast zinc |
| Fixing Mode | By the body |
| Movement of operating head | Rotary |
| Type of operator | Spring return without operating lever |
| Contact sequence number | 3 |
| Function Available | - |
| Switch actuation | CW and CCW From left or right |
| Type of approach | Lateral approach |
| Electrical connection | Screw-clamp terminals AWG 22...AWG 12 |
| Cable entry | 1 entry for Pg 13.5 DIN 40430 |
| Number of poles | 1 |
| Switch Function | SPDT-DB |
| Contact form | Form Z |
| Contact operation | Slow make slow break |
| Contacts usage | - |
| Contacts material | Silver flashed copper |
| Positive opening | Without |
| Minimum torque for tripping | 10 lbf.in (1.13 N.m) |
| Maximum actuation speed | 130 Ft/Min with 30° cam angle, levers only 90 ft/min with 45° cam angle, levers only |
| Tripping angle | 9 ° |
| Maximum displacement angle | 89 ° |
| Repeat accuracy | +/- 0.004 in linear travel of cam on 1.5 in lever arm |
| Contact code designation | A600, AC (Ue = 600 V) Ie = 1.2 A NEMA rating designation A600, AC (Ue = 480 V) Ie = 1.5 A NEMA rating designation A600, AC (Ue = 240 V) Ie = 3 A NEMA rating designation A600, AC (Ue = 120 V) Ie = 6 A NEMA rating designation |
| [Ithe] conventional enclosed thermal current | 20 A |
| [Ui] rated insulation voltage | 600 V 3)IEC 609470-1 600 V 3)UL 508 600 V 3)CSA C22.2 No 14 |
| [Uimp] rated impulse withstand voltage | 2.5 KV AC for 1 minute CE 2.2 KV AC for 1 minute UL 2.64 kV AC for 1 minute CSA |
| Short-circuit protection | 20 A Bussmann class CC KTK-R-21 fuse non-time delay |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TWSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|-------------------------------|---|
| Width | 2.25 in (57.15 mm) |
| Height | 4.66 in (118.36 mm) |
| Depth | 3.41 in (86.61 mm) |
| Net Weight | 2.5 lb(US) (1.13 kg) |
| Terminals description ISO n°1 | B (right side contact) A (left side contact) |

Environment

| | |
|---------------------------------------|--|
| Shock resistance | 30 gn 9 ms IEC 60068-2-27 |
| Vibration resistance | 10 gn 10...55 Hz)IEC 60068-2-6 |
| NEMA degree of protection | NEMA 1 Nema type 250 NEMA 2 Nema type 250 NEMA 4 Nema type 250 NEMA 12 Nema type 250 NEMA 13 Nema type 250 |
| IP degree of protection | IP67 conforming to IEC 60529 |
| Electrical shock protection class | Class 0 IEC 61140 |
| Ambient Air Temperature for Operation | -10...185 °F (-23...85 °C) |
| Ambient Air Temperature for Storage | -10...185 °F (-23...85 °C) |
| Protective treatment | Corrosion resistant gray paint |


Ordering and shipping details

| | |
|-------------------|--------------------------------------|
| Category | 21497-9007 FT,T OILTIGHT AND FOUNDRY |
| Discount Schedule | DS1 |
| GTIN | 785901147527 |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.50 in (8.89 cm) |
| Package 1 Width | 6.40 in (16.256 cm) |
| Package 1 Length | 2.90 in (7.366 cm) |
| Package 1 Weight | 2.50 lb(US) (1.134 kg) |

Offer Sustainability

| | |
|--|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| Environmental Disclosure |  Product Environmental Profile |
| For all Reach Rohs enquiries contact us at | sustainability@tesensors.com |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|