



Main

Range of product	L525
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	L525
Associated complete product	L525
Movement of operating head	Rotary
Type of operator	Aluminium spring return roller pin lever length: 145.54 mm belt conveyor monitoring cylindrical roller pin
Type of roller	1 nylon lateral roller diameter: 31.75 mm
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By shifting conveyor belt
Net weight	0.05 kg

Environment

Ambient air temperature for operation	-29...85 °C
Ambient air temperature for storage	-29...85 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.556 cm
Package 1 Width	3.556 cm
Package 1 Length	14.986 cm
Package 1 Weight	136.078 g

Offer Sustainability

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------