



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch
Product specific application	Compact box
Device short name	9007C
Body type	Plug-in
Head type	Multi-directional head
Material	Metal
Fixing mode	By the body
Movement of operating head	Multi-directional
Type of operator	Acetal resin spring return wobble stick (-)
Switch actuation	By any moving part
Type of approach	Multi-directional approach, multi-directional approach
Electrical connection	Screw-clamp terminals (AWG 22...AWG 12), 1...2
Cable entry	1 entry for 1/2" - 14 NPT conforming to ANSI B1.20.1
Number of poles	1
Contacts type and composition	NC-NO
Contact operation	Snap action
Positive opening	Without
Sale per indivisible quantity	1

Complementary

Body material	Zinc
Head material	Zinc
Function available	-
Switch function	SPDT-DB
Contact form	Form Z
Contacts material	Silver contacts
Terminals description ISO n°1	(1-2)NC (3-4)NO
Tripping angle	10 °
Maximum displacement angle	90 °
[Ie] rated operational current	1.2 A at 600 V AC, A600 conforming to NEMA 1.5 A at 480 V AC, A600 conforming to NEMA 3 A at 240 V AC, A600 conforming to NEMA 6 A at 120 V AC, A600 conforming to NEMA 0.1 A at 600 V DC, Q600 conforming to NEMA 0.27 A at 250 V AC, Q600 conforming to NEMA 0.55 A at 125 V DC, Q600 conforming to NEMA
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	600 V (pollution degree 3) conforming to UL 508 for contact block 600 V (pollution degree 3) conforming to CSA C22.2 No 14 for contact block
[Uimp] rated impulse withstand voltage	2.5 KV AC 1 min conforming to CE 2.2 KV AC 1 min conforming to UL 2.64 kV AC 1 s conforming to CSA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither TWSS Holding nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Short-circuit protection	10 A by CC fuse, protection type: non-time delay
Electrical durability	1000000 cycles
Local signalling	without
Mechanical durability	10000000 cycles
Width	39.37 mm
Height	187.96 mm
Depth	45.47 mm
Net weight	0.57 kg

Environment

Shock resistance	60 gn for 9 ms conforming to IEC 60068-2-27
Vibration resistance	25 gn (f= 10...150 Hz) conforming to IEC 60068-2-6
NEMA degree of protection	NEMA 1 conforming to Nema type 250 NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 6P conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 13 conforming to Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Electrical shock protection class	Class 0 conforming to IEC 61140
Ambient air temperature for operation	-29...85 °C for standard environment
Ambient air temperature for storage	-29...85 °C
Environmental characteristic	Standard environment
Protective treatment	Epoxy powder coat

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	6.4 cm
Package 1 Length	24.9 cm
Package 1 Weight	462.7 g

Offer Sustainability

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------