

SM900A820000

Hyde Park, ultrasonic sensor cylindrical M30,
Sn8m, NO/NC, 12...24 VDC, 3 m



Main

Range of product	Hyde Park
Sensor type	Ultrasonic sensor
Series name	Superprox 900
Device short name	SM900
Sensor design	Cylindrical M30
Type of sensing window	Adjustable
Material	Plastic
Enclosure material	ULTEM
Front material	Glass epoxy
Type of output signal	Discrete
Discrete output function	1 NO or 1 NC programmable
ISO thread	M30 x 1.5
Wiring technique	4-wire
[Us] rated supply voltage	12...24 V DC with overload and short-circuit protection
Supply voltage limits	10...28 V DC
Discrete output type	NPN
Electrical connection	Cable, 3 m cable length
Product specific application	-

Complementary

[Sn] nominal sensing distance	8 m
[Sd] sensing range	0.203...8 m
[Sa] assured operating distance	0.203...8 m teach push-button
Maximum differential travel	12.7 mm
Blind zone	0...203 mm
Transmission frequency	75 kHz
Repeat accuracy	2.54 %
Beam angle	10 °
Minimum size of detected object	Cylinder diameter 50.8 mm - up to 4572 mm sensing distance
Current consumption	100 mA
Maximum switching current	100 mA with reverse polarity protection
Resistance to electrostatic discharge	8 kV level 4 conforming to IEC 61000-4-2
Height	30 mm
Width	43.18 mm
Depth	30 mm
Length	116.3 mm
Net weight	0.6 kg

Environment

Product certifications	UL
Marking	CE
NEMA degree of protection	NEMA 4X (indoor use only)
IP degree of protection	IP67
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-20...80 °C

Relative humidity	100 % without condensation
Vibration resistance	+/-1 mm conforming to IEC 60068-2-6 (f = 10...55 Hz)
Shock resistance	30 gn in all 3 axes for 11 ms conforming to IEC 60068-2-27
Resistance to electromagnetic fields	10 V/m level 3 conforming to IEC 61000-4-3
Resistance to fast transients	1 kV level 3 conforming to IEC 61000-4-4

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------