

# XCKJ10511H7

Limit switch, XC Standard, XCKJ, thermoplastic roller lever, 1NC+1 NO, snap action, 1/2NPT



## Main

|                               |                                                 |
|-------------------------------|-------------------------------------------------|
| Range of Product              | Telemecanique Limit switches XC Standard        |
| Series name                   | Standard format                                 |
| Product or Component Type     | Limit switch                                    |
| Device short name             | XCKJ                                            |
| Sensor design                 | Form A CENELEC EN 50041                         |
| Body type                     | Fixed                                           |
| Head type                     | Rotary head                                     |
| Material                      | Metal                                           |
| Body material                 | Zamak                                           |
| Head material                 | Zamak                                           |
| Fixing Mode                   | By the body                                     |
| Movement of operating head    | Rotary                                          |
| Type of operator              | Spring return roller lever thermoplastic        |
| Type of approach              | Lateral approach, 1 or 2 programmable direction |
| Cable entry                   | 1 entry tapped for 1/2" NPT cable gland         |
| Number of poles               | 2                                               |
| Contacts type and composition | 1 NC + 1 NO                                     |
| Contact operation             | Snap action                                     |

## Complementary

|                                              |                                                                                                                                                                                                                                                                  |
|----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switch actuation                             | By 30° cam                                                                                                                                                                                                                                                       |
| Electrical connection                        | Screw-clamp terminals 1 x 0.34...2 x 1.5 mm <sup>2</sup>                                                                                                                                                                                                         |
| Contacts insulation form                     | Zb                                                                                                                                                                                                                                                               |
| Number of steps                              | 1                                                                                                                                                                                                                                                                |
| Positive opening                             | With                                                                                                                                                                                                                                                             |
| Positive opening minimum torque              | 4.43 lbf.in (0.5 N.m)                                                                                                                                                                                                                                            |
| Minimum torque for tripping                  | 2.21 lbf.in (0.25 N.m)                                                                                                                                                                                                                                           |
| Maximum actuation speed                      | 4.92 ft/s (1.5 m/s)                                                                                                                                                                                                                                              |
| [Ie] rated operational current               | 3 A 240 V, AC-15, A300 IEC 60947-5-1 appendix A<br>0.27 A 250 V, DC-13, Q300 IEC 60947-5-1 appendix A                                                                                                                                                            |
| [Ithe] conventional enclosed thermal current | 10 A                                                                                                                                                                                                                                                             |
| [Ui] rated insulation voltage                | 300 VUL 508<br>500 V 3)IEC 60947-1<br>300 VCSA C22.2 No 14                                                                                                                                                                                                       |
| Maximum resistance across terminals          | 25 MOhm IEC 60255-7 category 3                                                                                                                                                                                                                                   |
| [Uimp] rated impulse withstand voltage       | 6 KV IEC 60664<br>6 KV IEC 60947-1                                                                                                                                                                                                                               |
| Short-circuit protection                     | 10 A cartridge fuse gG                                                                                                                                                                                                                                           |
| Electrical durability                        | 5000000 Cycles, DC-13, inductive, 120 V, 4 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C<br>5000000 Cycles, DC-13, inductive, 24 V, 10 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C<br>5000000 cycles, DC-13, inductive, 48 V, 7 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C |
| Mechanical durability                        | 30000000 cycles                                                                                                                                                                                                                                                  |
| Width                                        | 1.57 in (40 mm)                                                                                                                                                                                                                                                  |
| Height                                       | 3.03 in (77 mm)                                                                                                                                                                                                                                                  |
| Depth                                        | 1.73 in (44 mm)                                                                                                                                                                                                                                                  |

|                               |                        |
|-------------------------------|------------------------|
| Net Weight                    | 1.06 lb(US) (0.48 kg)  |
| Terminals description ISO n°1 | (21-22)NC<br>(13-14)NO |

## Environment

|                                       |                                                                                                               |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------|
| Shock resistance                      | 50 gn 11 ms IEC 60068-2-27                                                                                    |
| Vibration resistance                  | 25 gn 10...500 Hz)IEC 60068-2-6                                                                               |
| IP degree of protection               | IP66 conforming to IEC 60529                                                                                  |
| IK degree of protection               | IK07 conforming to IEC 62262                                                                                  |
| Overvoltage category                  | Class I IEC 61140<br>Class I NF C 20-030                                                                      |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C)                                                                                    |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                                                                    |
| Protective treatment                  | TH                                                                                                            |
| Product Certifications                | UL[RETURN]CSA[RETURN]CCC                                                                                      |
| Standards                             | IEC 60947-5-1<br>IEC 60204-1<br>CENELEC EN 50041<br>IEC 60204-1<br>CSA C22.2 No 14<br>UL 508<br>IEC 60947-5-1 |

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US1000T22411  |
| Discount Schedule | 000T          |
| GTIN              | 3389118120839 |
| Returnability     | Yes           |
| Country of origin | FR            |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Number of Units in Package 1 | 1                       |
| Package 1 Height             | 1.65 in (4.200 cm)      |
| Package 1 Width              | 3.07 in (7.800 cm)      |
| Package 1 Length             | 5.51 in (14.000 cm)     |
| Package 1 Weight             | 16.79 oz (476.000 g)    |
| Unit Type of Package 2       | S02                     |
| Number of Units in Package 2 | 18                      |
| Package 2 Height             | 5.91 in (15 cm)         |
| Package 2 Width              | 11.81 in (30 cm)        |
| Package 2 Length             | 15.75 in (40 cm)        |
| Package 2 Weight             | 19.33 lb(US) (8.767 kg) |


## Offer Sustainability

|                                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status                   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| Circularity Profile                        | No need of specific recycling operations                                                                                                                                                                                                                                                                                                                                          |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>                                                                                                                                                                                                                                                                                                    |

## Contractual warranty


|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Dimensions



## Mounting with Cable Entry


### Position of Cable Gland



- (1) Recommended
- (2) To be avoided


## Mounting with Rotary Heads and Levers

### Type of Cam



- (1) Recommended
- (2) To be avoided

## Setting-up with Lever Head



- (1) 5° steps throughout 360° / Tightening torque (Min : 1) (Max : 1.5)
- (2) 45° steps throughout 360° / Tightening torque (Min : 1) (Max : 1.5)
- (a) Tightening torque (Min : 1) (Max : 1.5)

## Setting-up with Head ZCKE05

## Direction of Actuation Programming




---

Wiring Diagram


---

2-pole NC + NO Snap Action




## Characteristics of Actuation

### Switch Actuation on End



## Functionnal Diagram



(P) Positive opening point

(1) NC contact with positive opening operation

(2) Closed

(3) Open

(4) Tripping

(5) Resetting