

SM300A21600

Hyde Park, ultrasonic sensor cylindrical M12, Sn51mm, NO, 12...24 VDC, cable 3 m

Main

Range of product	Hyde Park
Sensor type	Ultrasonic sensor
Series name	Superprox 300
Device short name	SM300
Sensor design	Cylindrical M12
Type of sensing window	Fixed
Material	Plastic
Enclosure material	ULTEM
Front material	Glass epoxy
Type of output signal	Discrete
Discrete output function	1 NO
ISO thread	M12 x 1
Wiring technique	4-wire
[Us] rated supply voltage	12...24 V DC with overload and short-circuit protection
Supply voltage limits	10...28 V DC
Discrete output type	PNP/NPN
Electrical connection	Cable, 3 m cable length
Product specific application	-

Complementary

[Sn] nominal sensing distance	50.8 mm
[Sd] sensing range	25.4...50.8 mm
[Sa] assured operating distance	25.4...50.8 mm
Maximum differential travel	0.7 mm
Blind zone	0...6.4 mm
Transmission frequency	500 kHz
Repeat accuracy	0.7 %
Beam angle	8 °
Minimum size of detected object	Cylinder diameter 2.5 mm - up to 1 mm sensing distance
Current consumption	25 mA
Maximum switching current	100 mA with reverse polarity protection
Resistance to electrostatic discharge	8 kV level 4 conforming to IEC 61000-4-2
Height	12 mm
Width	12 mm
Depth	12 mm
Length	53.08 mm
Net weight	0.08 kg

Environment

Product certifications	UL
Marking	CE
NEMA degree of protection	NEMA 4X (indoor use only)
IP degree of protection	IP67
Ambient air temperature for operation	-30...70 °C
Ambient air temperature for storage	-40...100 °C

Relative humidity	100 % without condensation
Vibration resistance	+/-1 mm conforming to IEC 60068-2-6 (f = 10...55 Hz)
Shock resistance	30 gn in all 3 axes for 11 ms conforming to IEC 60068-2-27
Resistance to electromagnetic fields	10 V/m level 3 conforming to IEC 61000-4-3
Resistance to fast transients	1 kV level 3 conforming to IEC 61000-4-4

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.288 cm
Package 1 Width	6.35 cm
Package 1 Length	14.288 cm
Package 1 Weight	31.752 g

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------