


XC2JC101

Limit switch, Limit switches XC Standard, 600 VDC 10 amp XC2J +options



Main

| | |
|------------------------------|--------------------------------|
| Range of Product | OsiSense XC |
| Series name | Special format |
| Product or Component Type | Limit switch |
| Product Specific Application | For severe applications |
| Device short name | XC2J |
| Body type | Fixed |
| Head type | Rotary head |
| Material | Metal |
| Movement of operating head | Rotary |
| Type of operator | Roller lever thermoplastic |
| Switch actuation | By 30° cam |
| Type of approach | Lateral approach, 2 directions |
| Number of poles | 1 |
| Contact operation | Snap action |
| Minimum torque for tripping | 2.66 lbf.in (0.3 N.m) |
| Maximum actuation speed | 4.92 ft/s (1.5 m/s) |

Complementary

| | |
|-------------------------------------|--|
| Fixing Mode | By the body |
| Electrical connection | Screw-clamp terminals 1 x 0.5...2 x 2.5 mm ² |
| Cable entry | 1 entry incorporating cable gland 0.24...0.53 in (6...13.5 mm) |
| Contacts insulation form | Za |
| Contacts material | Silver plated contacts |
| Positive opening | Without |
| Minimum actuation speed | 0.001 m/min |
| Contact code designation | A300, AC-15 (Ue = 240 V), Ie = 3 A 10 A EN/IEC 60947-5-1 Q300, DC-13 (Ue = 250 V), Ie = 0.27 A EN/IEC 60947-5-1 |
| [Ui] rated insulation voltage | 500 VIEC 60947-5-1 500 VNF C 20-040 group C 300 VCSA C22.2 No 14 |
| Maximum resistance across terminals | 25 MOhm IEC 60255-7 category 3 25 MOhm NF C 93-050 method A |
| Short-circuit protection | 10 A cartridge fuse gG |
| Electrical durability | 5000000 Cycles, DC-13, 120 V, 4 W 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13, 24 V, 10 W 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 5000000 cycles, DC-13, 48 V, 7 W 3600 cyc/h 0.5 IEC 60947-5-1 appendix C |
| Mechanical durability | 30000000 cycles |
| Width | 1.57 in (40 mm) |
| Height | 5.55 in (141 mm) |
| Depth | 2.56 in (65 mm) |
| Net Weight | 1.33 lb(US) (0.605 kg) |
| Terminals description ISO n°1 | (13-14-11-12)OF |

Environment

| | |
|---------------------------------------|--|
| Shock resistance | 25 gn 18 ms IEC 60068-2-27 |
| Vibration resistance | 10 gn 10...500 Hz)IEC 60068-2-6 |
| IP degree of protection | IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010 |
| IK degree of protection | IK08 |
| Electrical shock protection class | Class I IEC 60536 Class I NF C 20-030 |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C) |
| Ambient Air Temperature for Storage | -40...158 °F (-40...70 °C) |
| Protective treatment | TC |
| Product Certifications | NEMKO[RETURN]CSA[RETURN]DEMKO |
| Standards | VDE 0660-200 UL 508 IEC 60337-1 CSA C22.2 No 14 EN/IEC 60947-5-1 |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US1000T22449 |
| Discount Schedule | 000T |
| GTIN | 3389110334227 |
| Returnability | No |
| Country of origin | FR |

Packing Units

| | |
|------------------------------|--------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.76 in (7.0 cm) |
| Package 1 Width | 1.77 in (4.5 cm) |
| Package 1 Length | 5.71 in (14.5 cm) |
| Package 1 Weight | 21.06 oz (597.0 g) |

Offer Sustainability

| | |
|--|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| Circularity Profile | No need of specific recycling operations |
| For all Reach Rohs enquiries contact us at | sustainability@tesensors.com |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|