

# XCNR2118G11

Limit switch, Limit switches XC Standard, XCNR, thermoplastic roller lever, 1NC+1 NO, snap, Pg11



## Main

|                               |                                          |
|-------------------------------|------------------------------------------|
| Range of product              | Telemecanique Limit switches XC Standard |
| Series name                   | Standard format                          |
| Product or component type     | Limit switch                             |
| Device short name             | XCNR                                     |
| Sensor design                 | Compact                                  |
| Reset                         | With                                     |
| Body type                     | Fixed                                    |
| Head type                     | Rotary head                              |
| Material                      | Plastic                                  |
| Body material                 | Plastic                                  |
| Head material                 | Plastic                                  |
| Fixing mode                   | By the body                              |
| Movement of operating head    | Rotary                                   |
| Type of operator              | Spring return roller lever thermoplastic |
| Type of approach              | Lateral approach, 2 directions           |
| Number of poles               | 2                                        |
| Contacts type and composition | 1 NC + 1 NO                              |
| Contact operation             | Snap action                              |

## Complementary

|                                        |                                                                                                                                                                             |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switch actuation                       | By 30° cam                                                                                                                                                                  |
| Electrical connection                  | Screw-clamp terminals, clamping capacity: 1 x 0.34...2 x 1.5 mm <sup>2</sup>                                                                                                |
| Cable entry                            | 1 entry tapped for Pg 11 cable gland                                                                                                                                        |
| Contacts insulation form               | Zb                                                                                                                                                                          |
| Positive opening                       | With                                                                                                                                                                        |
| Positive opening minimum torque        | 0.15 N.m                                                                                                                                                                    |
| Minimum torque for tripping            | 0.1 N.m                                                                                                                                                                     |
| Maximum actuation speed                | 1.5 m/s                                                                                                                                                                     |
| Contact code designation               | A300, AC-15 (Ue = 240 V), Ie = 3 A, Ithe = 10 A conforming to EN/IEC 60947-5-1 appendix A<br>R300, DC-13 (Ue = 250 V), Ie = 0.1 A conforming to EN/IEC 60947-5-1 appendix A |
| [Ui] rated insulation voltage          | 300 V conforming to UL 508<br>500 V (pollution degree 3) conforming to EN/IEC 60947-1<br>300 V conforming to CSA C22.2 No 14                                                |
| [Uimp] rated impulse withstand voltage | 6 KV conforming to IEC 60664<br>6 kV conforming to IEC 60947-1                                                                                                              |
| Short-circuit protection               | 10 A cartridge fuse, type gG                                                                                                                                                |
| Mechanical durability                  | 100000 cycles                                                                                                                                                               |

## Environment

|                                       |                                                                                         |
|---------------------------------------|-----------------------------------------------------------------------------------------|
| Shock resistance                      | 50 gn for 11 ms conforming to IEC 60068-2-27                                            |
| Vibration resistance                  | 25 gn (f= 10...500 Hz) conforming to IEC 60068-2-6                                      |
| IP degree of protection               | IP65 conforming to IEC 60529                                                            |
| IK degree of protection               | IK04 conforming to EN 50102                                                             |
| Electrical shock protection class     | Class II conforming to IEC 61140<br>Class II conforming to NF C 20030                   |
| Ambient air temperature for operation | -25...70 °C                                                                             |
| Ambient air temperature for storage   | -40...70 °C                                                                             |
| Protective treatment                  | TC                                                                                      |
| Product certifications                | UL[RETURN]CCC[RETURN]CSA                                                                |
| Standards                             | CSA C22.2 No 14<br>IEC 60204-1<br>IEC 60947-5-1<br>UL 508<br>EN 60204-1<br>EN 60947-5-1 |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 11.0 cm  |
| Package 1 Width              | 16.0 cm  |
| Package 1 Length             | 31.0 cm  |
| Package 1 Weight             | 106.0 g  |
| Unit Type of Package 2       | BB1      |
| Number of Units in Package 2 | 20       |
| Package 2 Height             | 11.0 cm  |
| Package 2 Width              | 16.0 cm  |
| Package 2 Length             | 31.0 cm  |
| Package 2 Weight             | 2.13 kg  |
| Unit Type of Package 3       | PAL      |
| Number of Units in Package 3 | 480      |
| Package 3 Height             | 60.0 cm  |
| Package 3 Width              | 80.0 cm  |
| Package 3 Length             | 480.0 cm |
| Package 3 Weight             | 88.8 kg  |


## Offer Sustainability

|                                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status                   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>                                                                                                                                                                                                                                                                                                    |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Dimensions




- (1) 1 tapped entry for Pg 11 cable gland  
(2) Ø: 2 elongated holes Ø 4.3 x 6.3 on 22 mm centres, 2 holes Ø 4.3 on 20 mm centres.

---

## Mounting with Cable Entry

---

### Position of Cable Gland




- (1) Recommended
- (2) To be avoided

---

## Mounting with Rotary Heads and Levers

---

### Type of Cam




- (1) Recommended
- (2) To be avoided

---

## Wiring Diagrams


---

2-pole NC + NO Snap Action




## Characteristics of Actuation

### Switch Actuation by 30° Cam



## Functionnal Diagram



- (P) Positive opening point
- (1) NC contact with positive opening operation
- (2) Closed
- (3) Open
- (4) Tripping
- (5) Resetting