

XMLF250D2115

pressure sensor 250 bar - G1/4 (female) - 24 V
- 0..10 V



Main

Range of product	Telemecanique Pressure sensors XM
Product or component type	Electronic pressure sensors
Pressure sensor name	XMLF
Wiring technique	3-wire
Pressure rating	250 bar
Fluid connection type	G 1/4 (female) conforming to ISO 228
Controlled fluid	Air (-15...80 °C) Corrosive fluid (-15...80 °C) Hydraulic oil (-15...80 °C) Fresh water (0...80 °C)
Type of output signal	Analogue
Analogue output function	0...10 V
Electrical connection	Male connector M12, 4 pins
Product specific application	-
Destruction pressure	1500 bar
Type of installation	Control circuit
Maximum switching current	200 mA
[Us] rated supply voltage	24 V DC, voltage limits: 17...33 V
Materials in contact with fluid	Stainless steel type AISI 303 FPM (Viton)

Complementary

Setting	External setting
Maximum permissible accidental pressure	1000 bar
Local display	With
Protection type	Short-circuit protection Connection faults Overload protection Reverse polarity
Current consumption	80 mA
Operating rate in Hz	50 Hz
Drift of the sensitivity	+/- 0.03 % of measuring range/°C
Drift of the zero point	+/- 0.1 % of measuring range/°C
Response time on output	5...500 ms, in steps of 1 ms
Mechanical durability	10000000 cycles
Display response time type	Fast Slow Normal
Height	113 mm
Depth	58 mm
Width	46 mm
Net weight	0.59 kg
Surge withstand	0.5 kV DC
Measurement accuracy	<= 0.6 % of the measuring range
Repeat accuracy	0.5 %

Environment

Operating position	Any position
Standards	EN/IEC 61000-4-4 EN/IEC 61000-4-8 EN 50082 EN/IEC 61000-4-6 EN/IEC 61000-4-3 EN 50081 EN/IEC 61000-4-5 EN/IEC 61000-6-2 EN/IEC 60947-5-1 EN/IEC 61000-4-11 EN/IEC 60947-1 EN/IEC 61000-4-2 CE
Product certifications	CSA[RETURN]UL
Ambient air temperature for operation	-25...80 °C
Vibration resistance	35 gn (f= 60...2000 Hz) conforming to EN/IEC 60068-2-6 5 gn (f= 25...200 Hz) conforming to EN/IEC 60068-2-6
Protective treatment	TC
Shock resistance	50 gn conforming to EN/IEC 60068-2-27
Resistance to fast transients	2 kV conforming to EN/IEC 61000-4-4
IP degree of protection	IP67 conforming to EN/IEC 60529
NEMA degree of protection	NEMA 4 NEMA 12 NEMA 6 NEMA 13
Resistance to electrostatic discharge	4 KV on contact conforming to EN/IEC 61000-4-2 8 kV in air conforming to EN/IEC 61000-4-2
Resistance to electromagnetic fields	10 V/m conforming to EN/IEC 61000-4-3
Resistance to conducted disturbances	10 V conforming to EN/IEC 61000-4-6

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------