



Main

Range of Product	Telemecanique Radio frequency identification XG
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or Component Type	Ethernet copper cable
Product Compatibility	XUW XGSZ33ETH XGSZ33EIP
Accessory / separate part destination	Ethernet network

Complementary

Cable length	9.84 ft (3 m)
Transmission rate	100 Mbit/s
Transmission support medium	2 twisted shielded pairs
Communication network category	5e
AWG Gauge	AWG 26
Electrical connection	1 male connector, M12 straight 4 D coding 1 male connector, RJ45 straight 4
Conductor material	Copper
Cover Material	PUR

Environment

IP Degree of Protection	IP67
Standards	EIA/TIA-568 IEC 60754-1 ISO/IEC 11801 Ed.2, 2002

Ordering and shipping details

Category	US10DS222491
Discount Schedule	0DS2
GTIN	3389119075626
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.34 in (3.400 cm)
Package 1 Width	7.20 in (18.300 cm)
Package 1 Length	7.28 in (18.500 cm)
Package 1 Weight	5.43 oz (154.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)

Package 2 Length	15.75 in (40 cm)
Package 2 Weight	4.12 lb(US) (1.871 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------

Wiring Diagram

