

# XMLA002B2S11

pressure switch XMLA 2.5 bar - fixed scale 1  
threshold - 1 C/O



## Main

|                                                         |                                                                                                                                                                                         |
|---------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range of product                                        | Telemecanique Pressure sensors XM                                                                                                                                                       |
| Product or component type                               | Electromechanical pressure sensor                                                                                                                                                       |
| Pressure sensor type                                    | Electromechanical pressure sensor                                                                                                                                                       |
| Device short name                                       | XMLA                                                                                                                                                                                    |
| Pressure rating                                         | 2.5 bar                                                                                                                                                                                 |
| Controlled fluid                                        | Air (0...160 °C)<br>Fresh water (0...160 °C)<br>Hydraulic oil (0...160 °C)                                                                                                              |
| Fluid connection type                                   | G 1/4 (female) conforming to ISO 228                                                                                                                                                    |
| Electrical connection                                   | Screw-clamps terminals, 1 x 0.5...2 x 2.5 mm <sup>2</sup>                                                                                                                               |
| AWG gauge                                               | AWG 20...AWG 14                                                                                                                                                                         |
| Cable entry                                             | Cable gland 9...13 mm                                                                                                                                                                   |
| Contacts type and composition                           | 1 C/O                                                                                                                                                                                   |
| Product specific application                            | -                                                                                                                                                                                       |
| Pressure switch type of operation                       | Detection of 1 single threshold                                                                                                                                                         |
| Electrical circuit type                                 | Control circuit                                                                                                                                                                         |
| Scale type                                              | Fixed differential                                                                                                                                                                      |
| Local display                                           | With                                                                                                                                                                                    |
| Adjustable range of switching point on rising pressure  | 0.15...2.5 bar                                                                                                                                                                          |
| Adjustable range of switching point on falling pressure | 0.02...2.37 bar                                                                                                                                                                         |
| Maximum permissible accidental pressure                 | 9 bar                                                                                                                                                                                   |
| Destruction pressure                                    | 18 bar                                                                                                                                                                                  |
| Pressure actuator                                       | Diaphragm                                                                                                                                                                               |
| Materials in contact with fluid                         | Steel<br>FPM, FKM                                                                                                                                                                       |
| Enclosure material                                      | Zinc alloy                                                                                                                                                                              |
| [In] rated current                                      | 3 A, B300, AC-15 (Ue = 120 V) conforming to IEC 60947-5-1<br>1.5 A, B300, AC-15 (Ue = 240 V) conforming to IEC 60947-5-1<br>0.1 A, R300, DC-13 (Ue = 250 V) conforming to IEC 60947-5-1 |

## Complementary

|                                          |                                                                                                      |
|------------------------------------------|------------------------------------------------------------------------------------------------------|
| Natural differential at low setting      | 0.13 bar (+/- 0.03 bar)                                                                              |
| Natural differential at high setting     | 0.13 bar (+/- 0.03 bar)                                                                              |
| Maximum permissible pressure - per cycle | 5 bar                                                                                                |
| Terminal block type                      | 4 terminals                                                                                          |
| Maximum operating rate                   | 120 cyc/mn                                                                                           |
| Repeat accuracy                          | 2 %                                                                                                  |
| [Ui] rated insulation voltage            | 300 V conforming to UL 508<br>500 V conforming to IEC 60947-1<br>300 V conforming to CSA C22.2 No 14 |
| [Uimp] rated impulse withstand voltage   | 6 kV conforming to IEC 60947-1                                                                       |

|                                     |                                                                                          |
|-------------------------------------|------------------------------------------------------------------------------------------|
| Auxiliary contacts operation        | Snap action                                                                              |
| Contacts material                   | Silver contacts                                                                          |
| Maximum resistance across terminals | 25 MOhm conforming to IEC 255-7 category 3<br>25 mOhm conforming to NF C 93-050 method A |
| Short-circuit protection            | 10 A cartridge fuse, type gG (gl)                                                        |
| Mechanical durability               | 8000000 cycles                                                                           |
| Setting                             | External                                                                                 |
| Height                              | 158 mm                                                                                   |
| Depth                               | 77.5 mm                                                                                  |
| Width                               | 35 mm                                                                                    |
| Net weight                          | 0.995 kg                                                                                 |

## Environment

|                                       |                                                                                                      |
|---------------------------------------|------------------------------------------------------------------------------------------------------|
| Standards                             | UL 508<br>CE<br>CSA C22.2 No 14<br>IEC 60947-5-1                                                     |
| Product certifications                | LROS (Lloyds register of shipping)<br>[RETURN]CCC[RETURN]UL[RETURN]CSA[RETURN]BV                     |
| Protective treatment                  | TC standard version                                                                                  |
| Ambient air temperature for operation | -25...70 °C                                                                                          |
| Ambient air temperature for storage   | -40...70 °C                                                                                          |
| Operating position                    | Any position                                                                                         |
| Vibration resistance                  | 4 gn conforming to IEC 60068-2-6 (f = 30...500 Hz)                                                   |
| Shock resistance                      | 50 gn conforming to IEC 60068-2-27                                                                   |
| Electrical shock protection class     | Class I conforming to IEC 1140<br>Class I conforming to IEC 536<br>Class I conforming to NF C 20-030 |
| IP degree of protection               | IP66 conforming to IEC 60529                                                                         |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 14.2 cm  |
| Package 1 Width              | 10.5 cm  |
| Package 1 Length             | 6.0 cm   |
| Package 1 Weight             | 1.154 kg |

## Offer Sustainability

|                                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status                   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| Circularity Profile                        | No need of specific recycling operations                                                                                                                                                                                                                                                                                                                                          |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>                                                                                                                                                                                                                                                                                                    |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|




---


## Wiring Diagram

---


### Terminal Model



## Operating Curves



(y) Rising pressure  
(x) Falling pressure



(y) Pressure  
(x) Time  
(1) Adjustable value  
(2) Non adjustable value  
PH : High point  
PB : Below point