

# XS608B1PAM8

inductive sensor XS6 M8 - L58mm - stainless -  
Sn2.5mm - 12..48VDC - M8



## Main

|                                    |                                                              |
|------------------------------------|--------------------------------------------------------------|
| Range of product                   | Telemecanique Inductive proximity sensors XS                 |
| Series name                        | General purpose                                              |
| Sensor type                        | Inductive proximity sensor                                   |
| Sensor name                        | XS6                                                          |
| Sensor design                      | Cylindrical M8                                               |
| Size                               | 58 mm                                                        |
| Body type                          | Fixed                                                        |
| Detector flush mounting acceptance | Flush mountable                                              |
| Material                           | Stainless steel                                              |
| Type of output signal              | Discrete                                                     |
| Wiring technique                   | 3-wire                                                       |
| [Sn] nominal sensing distance      | 2.5 mm                                                       |
| Discrete output function           | 1 NO                                                         |
| Output circuit type                | DC                                                           |
| Discrete output type               | PNP                                                          |
| Electrical connection              | Male connector M8, 3 pins                                    |
| [Us] rated supply voltage          | 12...48 V DC with reverse polarity protection                |
| Switching capacity in mA           | <= 200 mA DC with overload and short-circuit protection      |
| IP degree of protection            | IP67 conforming to IEC 60529<br>IP65 conforming to IEC 60529 |

## Complementary

|                        |                              |
|------------------------|------------------------------|
| Thread type            | M8 x 1                       |
| Detection face         | Frontal                      |
| Front material         | PPS                          |
| Enclosure material     | Stainless steel 303          |
| Sensing range          | > 0...2.5 mm                 |
| Operating zone         | 0...2 mm                     |
| Differential travel    | 1...15% of Sr                |
| Status LED             | Output state: 1 LED (yellow) |
| Supply voltage limits  | 10...58 V DC                 |
| Switching frequency    | <= 2500 Hz                   |
| Maximum voltage drop   | <2 V (closed)                |
| Current consumption    | <= 10 mA no-load             |
| Maximum delay first up | 10 ms                        |
| Maximum delay response | 0.2 ms                       |
| Maximum delay recovery | 0.2 ms                       |
| Marking                | CE                           |
| Threaded length        | 43 mm                        |
| Length                 | 58 mm                        |
| Net weight             | 0.015 kg                     |

## Environment

|                                       |                                                                         |
|---------------------------------------|-------------------------------------------------------------------------|
| Product certifications                | UL[RETURN]CSA                                                           |
| Ambient air temperature for operation | -25...70 °C                                                             |
| Ambient air temperature for storage   | -40...85 °C                                                             |
| Vibration resistance                  | 25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance                      | 50 gn for 11 ms conforming to IEC 60068-2-27                            |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 2 cm    |
| Package 1 Width              | 14.5 cm |
| Package 1 Length             | 20 cm   |
| Package 1 Weight             | 25 g    |

## Offer Sustainability

|                                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status                   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| Circularity Profile                        |  <a href="#">End of Life Information</a>                                                                                                                                                                                                                                                         |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>                                                                                                                                                                                                                                                                                                    |