

# XMLP025BC71F

Electronic pressure sensors, Pressure sensors XM, transmitter, XMLP, 25 bar, G1/4 A male, 0...10 V, DIN, set of 1



## Main

|                           |                                                                                                                                            |
|---------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Range of product          | Telemecanique Pressure sensors XM                                                                                                          |
| Product or component type | Electronic pressure sensors                                                                                                                |
| Pressure sensor type      | Pressure transmitter                                                                                                                       |
| Pressure sensor name      | XMLP                                                                                                                                       |
| Electrical circuit type   | Control circuit                                                                                                                            |
| Pressure rating           | 25 bar                                                                                                                                     |
| Local display             | Without                                                                                                                                    |
| Controlled fluid          | Air (-30...135 °C)<br>Fresh water (0...135 °C)<br>Hydraulic oil (-30...135 °C)<br>Gas (-30...135 °C)<br>Refrigeration fluid (-30...135 °C) |
| Fluid connection type     | G 1/4A (male) conforming to DIN 3852-E                                                                                                     |
| Electrical connection     | 1 male connector EN 175301-803-A (ex DIN43650)<br>3 pins                                                                                   |
| [Us] rated supply voltage | 24 V DC SELV (voltage limits: 12...33 V)                                                                                                   |
| Current consumption       | < 7 mA                                                                                                                                     |
| Type of output signal     | Analogue                                                                                                                                   |
| Analogue output function  | 0...10 V, 3-wire                                                                                                                           |
| Quantity per set          | Set of 1                                                                                                                                   |
| Type of packing           | Individual                                                                                                                                 |

## Complementary

|                                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|-----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Pressure setting range                  | 0...25 bar                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Maximum permissible accidental pressure | 75 bar                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Destruction pressure                    | 150 bar                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Materials in contact with fluid         | Fluorocarbon FPM<br>Stainless steel AISI 316L                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Operating position                      | Any position                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Protection type                         | Reverse polarity<br>Load short-circuit                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Electromagnetic compatibility           | Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 2 kV<br>Electrostatic discharge immunity test conforming to IEC 61000-4-2 8 kV air, 4 kV contact<br>1.2/50 µs shock waves immunity test conforming to IEC 61000-4-5 1 kV 42 Ohm<br>Immunity to magnetic fields conforming to IEC 61000-4-8 100 A/m 50 Hz<br>Susceptibility to electromagnetic fields conforming to IEC 61000-4-3 10 V/m<br>80...3000 MHz<br>Radiated RF fields conforming to IEC 61000-4-6 10 V 0.01...80 MHz |
| [Uimp] rated impulse withstand voltage  | 0.5 kV                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Response time on output                 | <= 2 ms 10...90 % of full scale                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Measurement accuracy                    | +/- 0.5 % of the measuring range                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Resolution                              | 0.1 % of the measuring range                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Drift of the sensitivity                | +/- 0.02 % of measuring range/°K                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Drift of the zero point                 | +/- 0.02 % of measuring range/°K                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Mechanical durability                   | 10000000 cycles                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Net weight                              | 0.106 kg                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |

|          |         |
|----------|---------|
| Diameter | 26 mm   |
| Length   | 60.6 mm |

## Environment

|                                       |                                                      |
|---------------------------------------|------------------------------------------------------|
| Standards                             | IEC 61326-2-3<br>NSF ANSI 61                         |
| Product certifications                | RCM[RETURN]CE[RETURN]cULus                           |
| Protective treatment                  | TC                                                   |
| Ambient air temperature for operation | -30...85 °C                                          |
| Ambient air temperature for storage   | -50...100 °C                                         |
| Vibration resistance                  | 20 gn (f = 15...2000 Hz) conforming to IEC 60068-2-6 |
| Shock resistance                      | 100 gn for 11 ms conforming to IEC 60068-2-27        |
| IP degree of protection               | IP65 conforming to IEC 60529                         |

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type of Package 1       | PCE |
| Number of Units in Package 1 | 1   |

## Offer Sustainability

|                                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status                   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>                                                                                                                                                                                                                                                                                                    |

## Dimensions



(1) SW24 tightening torque  $\leq 25$  N.m / 221 lb-in

---

## Wiring Diagram

---

### 3-Wire Technique (0-10 V)



(a) V out

---

## Curves

---

