

# XS630B1PBL5

Inductive proximity sensors XS, inductive sensor XS6 M30, L62mm, brass, Sn15mm, 12...48 VDC, cable 5 m



## Main

|                                    |                                                                                 |
|------------------------------------|---------------------------------------------------------------------------------|
| Range of product                   | Telemecanique Inductive proximity sensors XS                                    |
| Series name                        | General purpose                                                                 |
| Sensor type                        | Inductive proximity sensor                                                      |
| Device application                 | Mobile equipment                                                                |
| Sensor name                        | XS6                                                                             |
| Sensor design                      | Cylindrical M30                                                                 |
| Size                               | 62 mm                                                                           |
| Body type                          | Fixed                                                                           |
| Detector flush mounting acceptance | Flush mountable                                                                 |
| Material                           | Metal                                                                           |
| Type of output signal              | Discrete                                                                        |
| Wiring technique                   | 3-wire                                                                          |
| [Sn] nominal sensing distance      | 15 mm                                                                           |
| Discrete output function           | 1 NC                                                                            |
| Output circuit type                | DC                                                                              |
| Discrete output type               | PNP                                                                             |
| Electrical connection              | Cable                                                                           |
| Cable length                       | 5 m                                                                             |
| [Us] rated supply voltage          | 12...48 V DC with reverse polarity protection                                   |
| Switching capacity in mA           | <= 200 mA DC with overload and short-circuit protection                         |
| IP degree of protection            | IP68 double insulation conforming to IEC 60529<br>IP69K conforming to DIN 40050 |

## Complementary

|                          |                              |
|--------------------------|------------------------------|
| Thread type              | M30 x 1.5                    |
| Detection face           | Frontal                      |
| Front material           | PPS                          |
| Enclosure material       | Nickel plated brass          |
| Sensing range            | > 8...15 mm                  |
| Operating zone           | 0...12 mm                    |
| Differential travel      | 1...15% of Sr                |
| Cable composition        | 3 x 0.34 mm <sup>2</sup>     |
| Wire insulation material | PVC                          |
| Status LED               | Output state: 1 LED (yellow) |
| Supply voltage limits    | 10...58 V DC                 |
| Switching frequency      | <= 500 Hz                    |
| Maximum voltage drop     | <2 V (closed)                |
| Current consumption      | <= 10 mA no-load             |
| Maximum delay first up   | 10 ms                        |
| Maximum delay response   | 0.6 ms                       |
| Maximum delay recovery   | 1.4 ms                       |
| Marking                  | CE                           |
| Threaded length          | 52 mm                        |

|            |         |
|------------|---------|
| Length     | 62 mm   |
| Net weight | 0.33 kg |

## Environment

|                                       |                                                                         |
|---------------------------------------|-------------------------------------------------------------------------|
| Product certifications                | E2[RETURN]UL[RETURN]CSA                                                 |
| Ambient air temperature for operation | -25...70 °C                                                             |
| Ambient air temperature for storage   | -40...85 °C                                                             |
| Vibration resistance                  | 25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance                      | 50 gn for 11 ms conforming to IEC 60068-2-27                            |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 4.400 cm  |
| Package 1 Width              | 10.800 cm |
| Package 1 Length             | 14.800 cm |
| Package 1 Weight             | 270.000 g |
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 14        |
| Package 2 Height             | 15 cm     |
| Package 2 Width              | 30 cm     |
| Package 2 Length             | 40 cm     |
| Package 2 Weight             | 4.097 kg  |


## Offer Sustainability

|                                            |                                                                                                                                                                                                                                                                                                                                                                                   |
|--------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status                   | Green Premium product                                                                                                                                                                                                                                                                                                                                                             |
| Circularity Profile                        |  <a href="#">End of Life Information</a>                                                                                                                                                                                                                                                       |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>                                                                                                                                                                                                                                                                                                    |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Dimensions




---

### Minimum Mounting Distances


---

Side by side




$e (1) \geq 30 \text{ mm}/1.18 \text{ in.}$

Face to face



$e (2) \geq 180 \text{ mm}/7.09 \text{ in.}$


Facing a metal object



$e (3) \geq 45 \text{ mm}/1.77 \text{ in.}$

## Wiring Schemes

PNP



BU : Blue

BN : Brown

BK : Black