


# XZCE13P124M

Adaptor, plastic, tapped hole Pg 13.5, for male connector, M12, 4 wire



## Main

Accessory / separate part designation	4-wire connector adaptor
Accessory / separate part category	Cabling accessories
Accessory / separate part type	Connector adaptor
Cable composition	4 x 0.34 mm <sup>2</sup>
Thread type	Pg 13.5
Line Rated Current	4 A

## Complementary

Cable length	3.94 in (100 mm)
Total number of wires	4
Electrical connection	1 male connector M12 5 straight
Cable connector fixing	Screw-on
Body material	Plastic
Insulation resistance	> 1000000000 Ohm
Maximum resistance across terminals	5000 mOhm
[Ue] rated operational voltage	250 V AC 300 V DC
Net Weight	0.04 lb(US) (0.02 kg)

## Environment

IP Degree of Protection	IP67
Ambient air temperature for operation	-13...176 °F (-25...80 °C)

## Ordering and shipping details

Category	US10DS322483
Discount Schedule	0DS3
GTIN	3389110835502
Returnability	No
Country of origin	PL

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.98 in (2.500 cm)
Package 1 Width	3.94 in (10.000 cm)
Package 1 Length	2.95 in (7.500 cm)
Package 1 Weight	0.35 oz (9.800 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Height	2.95 in (7.500 cm)
Package 2 Width	11.02 in (28.000 cm)
Package 2 Length	14.96 in (38.000 cm)

Package 2 Weight	34.67 oz (983.000 g)
Unit Type of Package 3	S02
Number of Units in Package 3	200
Package 3 Height	5.91 in (15 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	5.40 lb(US) (2.451 kg)


### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

### Contractual warranty

Warranty	18 months
----------	-----------

## Dimensions




(1) Pg 13.5 cable gland

---

## Connections and Schemes

---

### Connector



BN : Brown  
BK : Black  
BU : Blue  
WH : White