

# ZCKY41

Limit switch lever, Limit switches XC Standard, ZCKY, thermoplastic plastic roller variable length, -40...70 °C



## Main

|                            |  |
|----------------------------|--|
| Range of product           | Telemecanique Limit switches XC Standard                   |
| Series name                | Standard format  |
| Product or component type  | Limit switch lever   |
| Device short name          | ZCKY   |
| Product compatibility      | XCKS<br>XCKL<br>XCKM<br>XCKJ                               |
| Associated head            | ZCKE05<br>ZCKD05   |
| Movement of operating head | Rotary   |
| Type of operator           | Roller lever spring return thermoplastic (variable length) |
| Type of approach           | Lateral approach   |

## Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Positive opening | Without    |

## Environment

|                                       |   |
|---------------------------------------|---|
| Ambient air temperature for operation | -25...70 °C for standard environment<br>-40...70 °C for low temperature |
| Ambient air temperature for storage   | -40...70 °C standard environment<br>-40...70 °C low temperature         |
| Environmental characteristic          | Low temperature<br>Standard environment                                 |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 1.500 cm  |
| Package 1 Width              | 10.000 cm |
| Package 1 Length             | 5.000 cm  |
| Package 1 Weight             | 23.000 g  |
| Unit Type of Package 2       | S01       |
| Number of Units in Package 2 | 100       |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 15.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 2.566 kg  |

## Offer Sustainability

|  |   |
|--|---|
| Sustainable offer status                   | Green Premium product   |
| Circularity Profile                        | No need of specific recycling operations  |
| California proposition 65                  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| For all Reach Rohs enquiries contact us at | <a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|