

XUM4ANXB2

Photoelectric sensors XU, miniature, diffuse short, Smax=0.25 m, NPN, cable 2 m



Main

Range of Product	Telemecanique Photoelectric sensors XU
Series name	General purpose single mode
Electronic sensor type	Photo-electric sensor
Sensor name	XUM
Sensor design	Miniature
Detection system	Diffuse
Material	Plastic
Type of output signal	Discrete
Supply circuit type	DC
Wiring Technique	3-wire
Discrete output type	NPN
Discrete output function	1 NO or 1 NC programmable
Electrical connection	Cable
Cable length	6.56 ft (2 m)
Emission	Infrared diffuse
[Sn] nominal sensing distance	0.56 ft (0.17 m)

Complementary

Enclosure Material	PBT
Lens material	PMMA
Maximum sensing distance	0.82 ft (0.25 m)
Output Type	Solid state
Wire insulation material	PVC
Status LED	Stability 1 LED green) Output state 1 LED orange)
[Us] rated supply voltage	12...24 V DC reverse polarity protection
Supply voltage limits	10...30 V DC
Switching capacity in mA	<= 100 mA overload and short-circuit protection
Switching frequency	<= 1000 Hz
Maximum voltage drop	<2 V
Current consumption	20 mA no-load
Maximum delay first up	100 ms
Maximum delay response	0.5 ms
Maximum delay recovery	0.5 ms
Setting-up	Sensitivity by potentiometer
Depth	0.79 in (20 mm)
Height	1.30 in (33 mm)
Width	0.39 in (10 mm)
Net Weight	0.14 lb(US) (0.063 kg)

Environment

Product Certifications	cULus[RETURN]CE[RETURN]UKCA
Ambient Air Temperature for Operation	-22...131 °F (-30...55 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Relative humidity	35...95 %
Immunity to ambient light	40000 Lux sunlight 10000 lux incandescent light

Vibration resistance	9 gn +/- 1.5 mm 10...500 Hz)for every axis IEC 60068-2-6
Shock resistance	100 gn 11 ms) for every axis IEC 60068-2-27
IP degree of protection	IP67 IEC 60529 IP65 IEC 60529

Ordering and shipping details

Category	US10DS222481
Discount Schedule	0DS2
GTIN	3389110966299
Returnability	No
Country of origin	JP

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.500 cm)
Package 1 Width	3.94 in (10.000 cm)
Package 1 Length	7.09 in (18.000 cm)
Package 1 Weight	1.76 oz (50.000 g)
Unit Type of Package 2	S04
Number of Units in Package 2	160
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	21.92 lb(US) (9.942 kg)


Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------


Dimensions



- (1) : Setting potentiometer (sensitivity)
- (2) : Setting potentiometer (output)
- (3) : Reception
- (4) : Transmission

Connection and schema

Wiring diagram





BN (Brown) : (+)

BK (Black) : OUT/Output

BU (Blue) : (-)

Detection curves

Object size/sensing distance





(1) : Sensor

(2) : Object (white mat paper of A mm square)

(A) : Side length (mm)

(X) : Sensing distance (mm)

Lateral displacement




(1) : Sensor

(2) : Object (200 x 200 mm square white paper)

(X) : Sensing distance (mm)

(Y) : Lateral displacement (mm)

Excess gain



(1) : Operation level

(X) : Sensing distance (m)

(Y) : Excess gain