

Main

Range of Product	Telemecanique Cabling components
Accessory / separate part category	Cabling accessories
Accessory / separate part type	Connector
Electrical connection	Elbowed male connector M23, 19 pins
Collar material	Metal
Status LED	Without
Cable connection	Solder terminal 0.00 in ² (1 mm ²) 0.35...0.47 in (9...12 mm)

Complementary

Cable gland type	Pg 13.5
Cable connector fixing	Screw-on
[Ue] rated operational voltage	60 V AC 75 V DC
Line Rated Current	7.5 A
Enclosure Material	Metal
Minimum insulating resistance	10000000 GΩ
Contact resistance	5000 μOhm
Net Weight	0.33 lb(US) (0.15 kg)

Environment

IP Degree of Protection	IP65
Ambient air temperature for operation	-13...230 °F (-25...110 °C)

Ordering and shipping details

Category	US10DS222499
Discount Schedule	0DS2
GTIN	3389110833935
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.98 in (2.5 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	3.15 in (8.0 cm)
Package 1 Weight	5.93 oz (168.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	19.57 lb(US) (8.876 kg)


Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------

Dimensions



(1) Cable gland: no. 13 metal (Pg 13.5)

Connections and Schemes

