

ZCKE235

Limit switch head, Limit switches XC Standard, ZCKE, steel roller lever plunger, +120 Å°C



Main

Range of product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJD31H29 ZCKJD35H29 ZCKJ4H7 ZCKJ9H7 ZCKJ2 ZCKJ6H29 ZCKJD35H7 ZCKJ11H29 ZCKJD35 ZCKJ1 ZCKJ4 ZCKJD37 ZCKJD31H7 ZCKJD37H29 ZCKJD39H7 ZCKJ5H7 ZCKJ6 ZCKJ5 ZCKJ4H29 ZCKJ7H29 ZCKJ5H29 ZCKJD31 ZCKJ1H29 ZCKJ21H7 ZCKJ8 ZCKJ41H7 ZCKJ2H7 ZCKJ8H7 ZCKJD37H7 ZCKJ6H7 ZCKJD39H29 ZCKJ7 ZCKJ1H7 ZCKJ7H7 ZCKJ21H29 ZCKJ2H29 ZCKJ11 ZCKJ41 ZCKJ41H29 ZCKJ9H29 ZCKJ11H7 ZCKJ21 ZCKJD39 ZCKJ9 ZCKJ8H29
Movement of operating head	Linear
Type of operator	Roller lever plunger spring return metal
Type of approach	Lateral approach, 1 direction

Complementary

Switch actuation	By 30° cam
Positive opening	With
Net weight	0.195 kg
Head material	Metal

Environment

Ambient air temperature for operation	10...120 °C
Ambient air temperature for storage	10...120 °C
Environmental characteristic	High temperature

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.700 cm
Package 1 Width	5.700 cm
Package 1 Length	6.600 cm
Package 1 Weight	192.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	14
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	2.875 kg

Offer Sustainability

Sustainable offer status	Green Premium product
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------